

Article Number: 9.20.085

Product Range Safety equipment

Product Category

Stainless steel ball valve, not self-closing.
Push plate made of steel, powder-coated in green.
Water-bearing parts made of brass.
Including emergency sign (pictogram).
Water flow rate: 14 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation.
Required water connection: ½" internal thread.
Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2.
Tested and certified acc. to DIN-DVGW.

Stainless steel ball valve, not self-closing.
Push plate made of steel, powder-coated in green.
Water-bearing parts made of brass.
Including emergency sign (pictogram).
Water flow rate: 14 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation.
Required water connection: ½" internal thread.
Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2.
Tested and certified acc. to DIN-DVGW.

HW-category	Emergency products
Outer width approx.	80 mm
Outer depth approx.	330 mm
Outer height approx.	180 mm