

Article Number: 9.71.202

Product Range Safety equipment

Product Category

incl. impact protection,dust protection cover and emergency sign (pictogram).

Casing made of glass fiber reinforced plastic.

Water-bearing parts made of brass.

Water flow rate: 7 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation and backflow preventer.

Required water connection: 1/2" external thread.

Hose length 1500 mm.

Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2.

Tested and certified acc. to DIN-DVGW.

incl. impact protection,dust protection cover and emergency sign (pictogram).

Casing made of glass fiber reinforced plastic.

Water-bearing parts made of brass.

Water flow rate: 7 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation and backflow preventer.

Required water connection: 1/2" external thread.

Hose length 1500 mm.

Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2.

Tested and certified acc. to DIN-DVGW.

HW-category

Emergency products

Outer width approx.

80 mm

Outer depth approx.

80 mm

Outer height approx.

240 mm