

Article Number: 9.71.402

**Product Range** Safety equipment

**Product Category**

incl. impact protection, dust protection cover and emergency sign (pictogram).

2 shower heads 45° angled.

Handle with integrated locking trigger made of plastic, valve not self-closing.

Casing made of glass fiber reinforced plastic.

Water-bearing parts made of brass.

Water flow rate: 14 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation and backflow preventer.

Required water connection: ½" external thread.

Hose length 1500 mm.

Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2.

Tested and certified acc. to DIN-DVGW.

incl. impact protection, dust protection cover and emergency sign (pictogram).

2 shower heads 45° angled.

Handle with integrated locking trigger made of plastic, valve not self-closing.

Casing made of glass fiber reinforced plastic.

Water-bearing parts made of brass.

Water flow rate: 14 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation and backflow preventer.

Required water connection: ½" external thread.

Hose length 1500 mm.

Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2.

Tested and certified acc. to DIN-DVGW.

<b>HW-category</b>	Emergency products
<b>Outer width approx.</b>	80 mm
<b>Outer depth approx.</b>	150 mm
<b>Outer height approx.</b>	310 mm