

Article Number: 9.84.085

Product Range Safety equipment

Product Category

Piping and shower arm made of brass,
powder-coated in green.

Pull rod made of steel, powder-coated.

Stainless steel ball valve.

High-performance shower head made of
chemical-resistant plastic, self-draining.

Including emergency sign (pictogram).

Water flow rate: 50 l/min. at 1.5 - 3 bar flow
pressure, incl. automatic flow regulation.

Required water connection: $\frac{3}{4}$ " external thread.

Tested acc. to BGI/GUV-I 850-0, DIN 1988,
DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-1.

Tested and certified acc. to DIN-DVGW.

Piping and shower arm made of brass,
powder-coated in green.

Pull rod made of steel, powder-coated.

Stainless steel ball valve.

High-performance shower head made of
chemical-resistant plastic, self-draining.

Including emergency sign (pictogram).

Water flow rate: 50 l/min. at 1.5 - 3 bar flow
pressure, incl. automatic flow regulation.

Required water connection: $\frac{3}{4}$ " external thread.

Tested acc. to BGI/GUV-I 850-0, DIN 1988,
DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-1.

Tested and certified acc. to DIN-DVGW.

HW-category

Emergency products

Outer width approx.

500 mm

Outer depth approx.

565 mm