

Ausschreibungstext

Article Number: 9.84.095

Product Range Safety equipment

Product Category

Piping, shower arm, ball valve and pull rod made of stainless steel.

High-performance shower head made of stainless steel, self-draining.

Including emergency sign (pictogram).

Water flow rate: 50 l/min. at 1.5 - 3 bar flow pressure, incl. automatic flow regulation.

Required water connection: 3/4" internal thread.

Tested acc. to BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-1.

Tested and certified acc. to DIN-DVGW.

Piping, shower arm, ball valve and pull rod made of stainless steel.

High-performance shower head made of stainless steel, self-draining.

Including emergency sign (pictogram).

Water flow rate: 50 l/min. at 1.5 - 3 bar flow pressure, incl. automatic flow regulation.

Required water connection: 3/4" internal thread.

Tested acc. to BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-1.

Tested and certified acc. to DIN-DVGW.

HW-category

Emergency products

Outer width approx.

500 mm

Outer depth approx.

565 mm